

0.5" Travel, Fine Screw, Thru-Hole Ball Bearing Stage



32mm/1.25" Center drive stage and its X-Y-Z configuration

Stock **#33-476** 10 TO 12 DAYS

- 1 + **₹33,408.00**

ADD TO CART

Qty 1+
₹33,408.00

Volume Pricing
Request Quote

Get Product Downloads

Type of Movement: Linear (X)
Guide System: Ball Bearing
Type of Drive: Fine Screw (64 Pitch)
Drive Orientation: Center Drive
Type: English

Stage Size (mm): 31.8 x 32.5
Travel (inches): 0.5
Construction: Aluminium Stage
Graduation (inches): No
Height (inches): 0.50
Height (mm): 12.7
Load Capacity, Normal (lbs): 6
Note: Thru-Hole
Stage Size (inches): 1.25 x 1.28
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.16
Thrust Capacity, T_a (lbs): 10
Thrust Capacity, T_b (lbs): 3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View