

0.5" x 0.5" (200 lp/mm), Ronchi Ruling



Stock #66-345

10 TO 12 DAYS



1



₹26,100.00

ADD TO CART

Qty 1-4
₹26,100.00
Qty 5+
₹24,865.00
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Frequency (lp/mm):
200

Substrate:
Float Glass

Optical Density OD (Average): 3.00
Dimensions (inches): 0.5 x 0.5
Surface Quality: 60-40
Thickness (mm): 1.50
Type: Metric
Dimensional Tolerance (mm): ± 0.02
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View