

0.6 OD M25.5 x 0.50, Mounted Absorptive ND Filter



Stock **#59-168** CLEARANCE 10 TO 12 DAYS

-

1

+

₹2,779.65

ADD TO CART

Qty 1+
₹2,779.65

Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average): 0.6
Clear Aperture CA (mm): 21.0
Filter Thread: M25.5 x0.50
Substrate: ☐ ND Filter Glass
Thickness with Mount (mm): 4.50

Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 27.5 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View