

0.6 OD M37 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-564 10 TO 12 DAYS

⊖ 1 ⊕ **₹5,438**

ADD TO CART

Qty 1-9

₹5,438

Qty 10+

₹5,203

Volume Pricing

[Request Quote](#)

Get Product Downloads

Optical Density OD (Average):

0.6

Clear Aperture CA (mm):

32.50

Filter Thread:

M37 x 0.50

Substrate:

ND Filter Glass

Surface Quality:
40-20

Transmission (%):
25.00

Type:
Mounted Imaging Filter

Blocking Wavelength Range (nm):
425 - 675

Mount Thickness (mm):
5.2

Mount Thickness Including Threads (mm):
7.0

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
