

0.6 OD M77 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-411 10 TO 12 DAYS

- 1 + ₹14,703.00

ADD TO CART

Qty 1-9
₹14,703.00
Qty 10+
₹13,972.00
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
73.00

Filter Thread:
M77 x0.75

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 25.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
