

[All Products](#) / [Imaging Lenses](#) / [Zoom Lenses](#) / [Dynamic Focus VZM™ Lens](#)

[See all 5 Products in Family](#)

0.65X - 4.6X Dynamic Focus VZM™ Lens



Dynamic Focus VZM™ Lens

Stock **#89-999** CLEARANCE 10 TO 12 DAYS

- 1 +

₹126,754.65

ADD TO CART

Qty 1+
₹126,754.65
Volume Pricing
Request Quote

Get Product Downloads

Length (mm): 248.00
Filter Thread: M22.5 x 0.50
Working Distance Tolerance (mm): ±3
Zoom Ratio: 7:1
Type: Zoom Lens

Primary Magnification PMAG: 0.65X - 4.6X
Maximum Sensor Format: 2/3"
Working Distance (mm): 87.00
Style: Liquid Lens
Lens Wavelength Range: VS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
