

# 0.9" High Brightness LED Spot Light, 470nm, Strobed

See More by [Advanced Illumination](#)



Stock #83-298 [CONTACT US](#)

-

1

+

₹43,239.00

ADD TO CART

|            |
|------------|
| Qty 1+     |
| ₹43,239.00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

|                                      |
|--------------------------------------|
| <b>Color:</b><br>Blue                |
| <b>Diameter (mm):</b><br>22.90       |
| <b>Model Number:</b><br>SL073-470-IS |
| <b>Length (mm):</b><br>54.00         |

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Operating Temperature (°C):</b><br>0 to 65                                                                                                                                                                                               |
| <b>Wavelength (nm):</b><br>470.00                                                                                                                                                                                                           |
| <b>Working Distance (mm):</b><br>100.00                                                                                                                                                                                                     |
| <b>Intensity Control Option:</b><br>No                                                                                                                                                                                                      |
| <b>LED Lifetime (hours):</b><br>50,000                                                                                                                                                                                                      |
| <b>Wavelength Tolerance (nm):</b><br>±25                                                                                                                                                                                                    |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#66-855</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
| <b>Light Distribution (%):</b><br>±10 Edge to Edge (Dependent on Working Distance)                                                                                                                                                          |
| <b>Number of LEDs:</b><br>1 High Brightness                                                                                                                                                                                                 |
| <b>Number of Channels:</b><br>1.00                                                                                                                                                                                                          |
| <b>Field Coverage (mm):</b><br>43.00                                                                                                                                                                                                        |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Note:</b><br>Optional Manual Intensity Adjustment <a href="#">#86-887</a> and <a href="#">#89-555</a> are Available                                                                                                                      |
| <b>Manufacturer:</b><br>Advanced Illumination                                                                                                                                                                                               |
| <b>Geometry:</b><br>Spot Light                                                                                                                                                                                                              |
| <b>Illumination Mode:</b><br>Strobed                                                                                                                                                                                                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |