

0.9 OD M46.0 x 0.75, Mounted Absorptive ND Filter



Stock #54-740 10 TO 12 DAYS

- 1 +

₹3,741.00

ADD TO CART

Qty 1-9
₹3,741.00
Qty 10+
₹3,437.00
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
42.0

Filter Thread:
M46 x0.75

Substrate:
ND Filter Glass

Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 12.5
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 4.4 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 48.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.4

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View