

[See all 12 Products in Family](#)

# 1-1.75mm, 24-14TPI, Screw Thread Micrometer Anvil/Tip Set

See More by [Mitutoyo](#)



Stock #78-308 **1 In Stock**

MRP ₹10,726

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹10,726 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

24 - 14 TPI, 1 - 1.75mm **Range:**

V Anvil and Conical Spindle **Type:**

126-803 **Model Number:**

### Regulatory Compliance

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

Japan

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.