

[See all 11 Products in Family](#)

1-2", 0.00005", IP65 Digimatic Digital Micrometer, No Output, Ratchet Thimble

See More by [Mitutoyo](#)



Stock **#78-327** 1 In Stock

-

1

+

MRP ₹30,373

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹30,373 each
Need More?	Request Quote

Product Downloads	
±0.0005	Accuracy (inches):
General	
1 - 2 inches	Range:
Ratchet Thimble	Type:
Model Number:	

Physical & Mechanical Properties

Resolution (inches):
5E-05

Regulatory Compliance

ViewCertificate of Conformance:

Country of Origin:
Japan

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- IP65 Rated QuantuMke® and Digimatic® Models
 - Easy-to-Read Digital Display
 - 0-1", 1-2", and 2-3" Range Options
- Mitutoyo Digital Micrometers provide high accuracy and precision over several measurement ranges, making them ideal for a wide range of applications. The QuantuMke® and Digimatic® micrometer models feature an easy-to-read digital display to reduce the chance of errors and the QuantuMke® model features a rapid action micrometer that enables measurements to be made several times faster than a standard micrometer. Select models have a built-in SPC data output function allowing seamless integration with computers or printers for efficient data recording and analysis. Mitutoyo Digital Micrometers are designed with a friction thimble or ratchet stop to ensure consistent measuring pressure, improving repeatability. With IP65 protection, these micrometers are resistant to physical deterioration due to routine exposure to water, cutting oil or coolant.