

[All Products](#) / [Test Targets](#) / [Resolution Test Targets](#) / [Star Target](#)

[See all 4 Products in Family](#)

Siemens Star Target, 4" x 4", 120 Sectors Photo Paper



Photo Paper Star Target

Stock **#46-246** 10 TO 12 DAYS

⊖ 1 ⊕ **₹10,875.00**

ADD TO CART

Qty 1-4
₹10,875.00
Qty 5+
₹10,344.00
Volume Pricing
Request Quote

Get Product Downloads

Frequency (lp/mm): 0.6112 - 15.28
Substrate: Photo Paper
Line Width (mm): 0.033 - 0.818
Number of Sectors:

120.00
Optical Density OD (Average): >1.6
Pattern Diameter (mm): 62.5
Dimensions (inches): 4 x 4 ±0.004
Thickness (mm): 0.20 ±nominal
Wedge Angle: 3°
Unresolved Core Diameter (mm): 2.5
Note: Emulsion Coated
NIST Certification: No

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant