

TECHSPEC® 10" Diameter x 100" FL Protected Aluminum, Parabolic Mirror



Stock #35-726-522 10 TO 12 DAYS

- 1 +

₹193,314.00

ADD TO CART

Qty 1-2
₹193,314.00
Qty 3+
₹164,343.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate:
BOROFLOAT®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 10.00 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 100.0
Effective Focal Length EFL (mm): 2,540.00
Radius of Curvature (mm): 5,080.00
Aperture (f/#): f/10
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant