

TECHSPEC® 10" Diameter x 80" FL Protected Aluminum, Parabolic Mirror



Stock #32-275-522 [CONTACT US](#)

- 1 + **₹193,314.00**

ADD TO CART

Qty 1-2
₹193,314.00
Qty 3+
₹164,343.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 10.0 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 80.0
Effective Focal Length EFL (mm): 2,032.00
Radius of Curvature (mm): 4,064.00
Aperture (f/#): f/8
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror
Wavelength Range (μm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant