

10 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock #57-875 CLEARANCE 2 In Stock

MRP ₹42,480

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹42,480 each
Qty 5+	₹40,409 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Length (inches):
3.00

Pattern Size (mm):
12.7 x 25.4

Thickness (mm):
1.10

Width (inches):
1.00

Optical Properties

Coating:

Vacuum Deposited Chrome
Fluorescent Peak Excitation @ 365 nm; Fluorescent
Peak Emission @ 550 nm

Frequency (lp/mm):

10.00

Substrate:

[Fused Silica](#) with Fluorescent Backing

Optical Density OD (Average):

3.00

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 240:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.