

10 x 10mm, 300µm Pitch, 1.1° Divergence, Cyl. Microlens Array



Stock #86-840 10 TO 12 DAYS

- 1 +

₹61,335.00

ADD TO CART

Qty 1-10
₹61,335.00
Qty 11+
₹53,940.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
8.00

Substrate: [Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:
Lens Array

Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±1.1
Pitch (µm): 300.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 3.600
Thickness (mm): 1.20
Thickness Tolerance (mm): ±0.05

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View