

10 x 60° Diffusing Angle 8" x 8" Unmounted



Stock #55-445 10 TO 12 DAYS

- 1 +

₹39,803.00

ADD TO CART

Qty 1+
₹39,803.00

Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°): ±1 x ±6
Diffusing Angle (°): 10 x 60 (FWHM)
Dimensional Tolerance (mm): ±0.5
Dimensions (inches): 8 x 8
Dimensions (mm): 203.20 x 203.20

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Width (mm): 203.20
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)
Length (mm): 203.20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant