

[See all 16 Products in Family](#)

100 lp/mm, 1" x 3", Fused Silica, Ronchi Ruling



Stock **#57-888** CLEARANCE CONTACT US

- 1 + MRP ₹45,985

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹45,985 each
Qty 5+	₹43,712 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Length (inches):
3.00

Pattern Size (mm):
12.7 x 25.4

Thickness (mm):
1.10

Width (inches):
1.00

Optical Properties

Vacuum Deposited Chrome
Coating:

100.00
Frequency (lp/mm):

[Fused Silica](#) (Corning 7980)
Substrate:

3.00
Optical Density OD (Average):

Regulatory Compliance

[Compliant](#)
RoHS 2015:

[View](#)
Certificate of Conformance:

[Compliant](#)
Reach 240:

United States
Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.