

100 x 100mm, 1.1mm Thick, Uncoated, Dragontrail™ Chemically Strengthened Window



Stock #17-259 10 TO 12 DAYS

- 1 + ₹3,480.00

ADD TO CART

Qty 1-5
₹3,480.00
Qty 6+
₹2,784.00
Volume Pricing
Request Quote

Get Product Downloads

Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):
20

Clear Aperture (%):
90

Clear Aperture CA (mm):
90 x 90

Dimensions (mm): 100.00 x 100.00
Thickness (mm): 1.10 Nominal
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 9.8
Density (g/cm³): 2.48
Edges: Fine Ground
Index of Refraction n_d: 1.51
Poisson's Ratio: 0.23
Substrate: Dragontrail™
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 350 - 2000
Young's Modulus (GPa): 74
Length (mm): 100.00
Width (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant