

100 x 100mm 120 Grit Ground Glass Diffuser



Stock #83-384 **6 In Stock**

- 1 + MRP ₹5,297

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹5,297 each
Qty 11+	₹4,893 each
Need More?	Request Quote

Product Downloads

General

Ground Glass Diffuser **Type:**

Sandblasted on first surface **Note:**

Physical & Mechanical Properties

±0.25 **Dimensional Tolerance (mm):**

Dimensions (mm):

100.00 x 100.00

Cut **Edges:**

120 **Grit:**

1.60 **Thickness (mm):**

100.00 **Width (mm):**

100.00 **Length (mm):**

Optical Properties

Uncoated **Coating:**

Float Glass **Substrate:**

350 - 2000 **Wavelength Range (nm):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

United States **Country of Origin:**

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000


Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- **Fused Silica Substrates** Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts