

100 x 100mm 470nm, LED Backlight

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity LED Backlights

Stock **#66-836** [CONTACT US](#)

- 1 + **₹78,387.00**

ADD TO CART

Qty 1+

₹78,387.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Blue

Model Number:
BL040401-470-IC

Operating Temperature (°C):
0 to 65

Dimensions (mm):
123 H x 123 W x 19 D

Wavelength (nm): 470.00
LED Lifetime (hours): 50,000
Wavelength Tolerance (nm): ±25
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 192.00
Number of Channels: 1.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Uniformity (%): ±6 over Illuminated Area (Dependent on Working Distance)
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)