

100 x 100mm Left-Handed Circular Polarizing Film (CP42HE)



Stock **#88-087** CLEARANCE 10 TO 12 DAYS

-

1

+

₹4,263.00

ADD TO CART

Qty 1-5
₹4,263.00
Qty 6+
₹3,393.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [Polymer Film CP42HE](#)

Length (mm):
100.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
100.0 x 100.0

Thickness (mm): 0.27 ±0.04
Transmission (%): 42.00
Type: Left-Handed Circular Polarizer
Dimensional Tolerance (mm): +0.0/-1.0
Construction: Polarizing Film
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.90
Heat Resistance (°C x Hours): 80 x 500
Width (mm): 100.00
#Sorting: 22.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)