

100 x 150mm, Blue, EuroBrite™ Spot Light

See More by [Advanced Illumination](#)



Blue AI EuroBrite Spot Light

Stock **#33-455** [CONTACT US](#)

-

1

+

₹69,600.00

ADD TO CART

Qty 1+

₹69,600.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Blue

Operating Lifetime (hours):
50,000

Input Voltage (V):
24V nominal (min. 22 / max 28)

Model Number:
SL-S100150M470

Operating Temperature (°C): 0 - 60
Dimensions (mm): 150 x 139 x 30
Wavelength (nm): 470.00
Weight (g): 253.00
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (mm): 100 x 150
Type of Illumination: LED Illuminator
Note: See Technical Information Tab for Typical Intensity
Geometry: Spot Light
Maximum Input Current: 0.42 - 0.49A
Analog Intensity Control: 10% @ 0.7V, 100% @ 10V
Trigger-to-Pulse Latency: 10µm
Illumination Mode: Strobed or Constant
Environmental Rating: IP67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)