

[See all 14 Products in Family](#)

1000µm, Optical Grade Plastic Optical Fiber Unjacketed



Stock #02-534 **20+ In Stock**

⊖ 1 ⊕ MRP ₹212

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹212 each
Need More?	Request Quote

Product Downloads

General

Minimum Purchase is 10ft or Qty = 10 **Note:**

Physical & Mechanical Properties

25.00 **Minimum Bend Radius (mm):**

1.00 **Number of Fibers:**

1.0 **Outer Diameter (mm):**

980.00	Core Diameter (μm):
Cut to Order, Minimum 10	Length (ft):
Unjacketed	Construction:
± 6	Diameter Tolerance (%):

Optical Properties

61.00	Acceptance Angle ($^{\circ}$):
Acrylic	Substrate: <input type="checkbox"/>
0.15	Attenuation (dB/m):
0.51	Numerical Aperture NA:
1000.00	Fiber Diameter (μm):
1.492	Index of Refraction (n_d) - Core:
1.402	Index of Refraction (n_d) - Cladding:
150 - 300 (@650nm)	Attenuation (dB/km):
± 0.03	Numerical Aperture (NA) Tolerance:

Environmental & Durability Factors

-55 to +70	Operating Temperature ($^{\circ}\text{C}$):
------------	---

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Superior Light Transmission
- ESKA® Fiber Strands
- Step Index

Optical Grade Fiber Optics, developed and manufactured by Mitsubishi, are offered in two grades, both with superior optical properties for improved transmission. The core of both is made of acrylic polymer PMMA (polymethyl-methacrylate) and is sheathed with a particular thin layer of fluorine polymer which has a lower refractive index than the fiber core. Optical Grade Fiber Optics are designed to provide higher transmission in the visible region of the spectrum. They can be used for a wide range of applications, from general industrial light guides to short-distance data transmission. The fiber is tough and flexible but is not designed to bear loads.

Note: Price listed is per foot - minimum order is 10 feet per stock number. 3mm Fiber is lower grade ESKA® fiber for commercial applications only.

Technical Information



