

# 1000nm CWL, 10nm FWHM, 12.5mm Mounted Diameter



Stock #65-768 10 TO 12 DAYS

- 1 +

₹7,743.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹7,743.00                     |
| Qty 10+                       |
| ₹6,986.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
12.50 +0.0/-0.2

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥4.0

Clear Aperture CA (mm):

|                                                        |
|--------------------------------------------------------|
| 9.0                                                    |
| <b>Center Wavelength CWL (nm):</b><br>1,000.00 ±2      |
| <b>Center Wavelength CWL Tolerance (nm):</b><br>±2     |
| <b>Full Width-Half Max FWHM (nm):</b><br>10.00 ±2      |
| <b>Full Width-Half Max FWHM Tolerance (nm):</b><br>±2  |
| <b>Minimum Transmission (%):</b><br>>70                |
| <b>Operating Temperature (°C):</b><br>-50 to +75       |
| <b>Coating:</b><br>Traditional Coated                  |
| <b>Surface Quality:</b><br>80-50                       |
| <b>Thickness Tolerance (mm):</b><br>±0.1               |
| <b>Type:</b><br>Bandpass Filter                        |
| <b>Typical Applications:</b><br>Clinical Chemistry     |
| <b>Blocking Wavelength Range (nm):</b><br>200 - 1200   |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Mount Thickness (mm):</b><br>7.5 ±0.1               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---