

100mm Dia x 19mm FL Cold Mirror Coated, Parabolic Reflector



Stock #68-795

CONTACT US

-

1

+

₹42,195.00

ADD TO CART

Qty 1-10
₹42,195.00
Qty 11+
₹37,106.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate:

BOROFLOAT[®]

Diameter (mm):
100.00 +0.0/-0.5

Focal Length FL (mm):
19.00

Aperture (f#):
0.190

Coating: Cold Mirror, 0°
Coating Type: Metal
Center Hole Diameter (mm): 30.0
Height (mm): 32.0
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
