

75mm Max. Aperture, Iris Diaphragm



Stock #30-264 10 TO 12 DAYS

- 1 + ₹25,491.00

ADD TO CART

Qty 1-4
₹25,491.00
Qty 5+
₹22,533.00
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
4.5

Maximum Aperture (mm):
75.0

Outer Diameter (mm):
100.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 14.20
Number of Leaves: 20.00
Thickness (mm): 9.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)
