

100X DIN Achromatic Commercial Grade Objective



100X DIN Achromatic Commercial Grade Objective, #43-905

Stock **#43-905** 10 TO 12 DAYS

- 1 + **₹14,355.00**

ADD TO CART

Qty 1+
₹14,355.00

Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
2.91

Length excluding Threads (mm):
45.80

Magnification:
100X

Maximum Diameter (mm):
24

Numerical Aperture NA:
1.25

Mounting Threads: 0.7965-36 TPI, 55° Whitworth
Type: Achromatic, Spring-Loaded
Operating Temperature (°C): 5 to 40
Storage Temperature (°C): -20 to 60
Working Distance (mm): 0.1
Note: Recommended Immersion Oil #86-834
Style: Finite Conjugate
Parfocal Length (mm): 45.9
Immersion Liquid: Oil
Operating Relative Humidity: 45% to 85%

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
