

100X EO M Plan Apo ULWD Infinity Corrected



50XEOMPlan Apo Long Working Distance Infinity Corrected, #59-879

Stock **#59-882** 10 TO 12 DAYS

- 1 +

₹424,212.00

ADD TO CART

Qty 1+
₹424,212.00

Volume Pricing
Request Quote

Get Product Downloads

Field of View (mm): 0.24
Horizontal Field of View, 1/2" Sensor: 0.064mm
Horizontal Field of View, 2/3" Sensor: 0.088mm
Horizontal Field of View, 1" Sensor: 0.128mm
Focal Length FL (mm): 2.00

Length (mm): 82.00
Length excluding Threads (mm): 82.00
Magnification: 100X
Maximum Diameter (mm): 34
Numerical Aperture NA: 0.55
Mounting Threads: M26 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.5
Depth of Field (µm): 0.90
Field of View, 24 Diameter Field Eyepiece (mm): 0.24
Operating Temperature (°C): +10 to +40
Operating Humidity: <85% with no condensation
Working Distance (mm): 13.0
Weight (g): 340.00
Wavelength Range (nm): 390 - 780
Style: Infinity Corrected
Field Number (mm): 24
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View