

100x100mm Half Mirror Coaxial Light White

See More by [CCS](#)



Stock #21-838 1 In Stock

-

1

+

₹4,48,485

ADD TO CART

Volume Pricing	
Qty 1+	₹4,48,485 each
Need More?	Request Quote

Product Downloads

General	
LFV3-G-100SW	Model Number:
LED Illuminator	Type of Illumination:
CCS	Manufacturer:
Coaxial Light	Geometry:
Constant	Illumination Mode:

Physical & Mechanical Properties	
W 110 mm x D 183 mm x H 105 mm	Dimensions (mm):
990	Weight (g):
100 mm x 102 mm	Active Area (mm):
Optical Properties	
White	Color:
Electrical	
34	Power Consumption (W):
Hardware & Interface Connectivity	
24	Input Voltage (V):
Power Supply Required and Sold Separately. USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491	Power Supply:
Environmental & Durability Factors	
7000	Color Temperature (K):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Unique Design Prevents Ghost Images
- Available in Red, White, and Blue
- Ideal for Use with High Resolution Cameras

CCS High-Resolution Coaxial Lights are designed to provide diffused lighting for high-resolution imaging of shiny, flat surfaces. Designed to prevent ghost reflections and achieve higher system resolution, these coaxial lights integrate a unique thin beamsplitter to minimize deviation through in the imaging path. CCS High-Resolution Coaxial Lights are ideal for industrial imaging applications including inspection of glossy surfaces, pattern detection on PCBs, and measuring dimensions of glass.

Technical Information

