

101 x 127mm, Extended Hot Mirror



Extended Hot Mirrors

Stock **#47-304** 10 TO 12 DAYS

- 1 +

₹22,707.00

ADD TO CART

Qty 1-9
₹22,707.00
Qty 10+
₹19,880.00
Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°): 0.00
Coating: Hot Mirror, 0°
Substrate: ☐ BOROFLOAT®
Dimensions (mm):

101.0 x 127.0
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): ≥85
Edges: Seamed
Coating Specification: R _{avg} ≥90% @ 750 - 1150nm R _{avg} ≥80% @ 1200 - 1600nm T _{avg} ≥85% @ 425 - 675nm
Wavelength Range (nm): 425 - 1600
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant