

101.6 x 101.6 x 3mm High Efficiency Window



Stock #46-103 10 TO 12 DAYS

- 1 + ₹3,306.00

ADD TO CART

Qty 1-5
₹3,306.00
Qty 6+
₹2,654.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm):

91.44 x 91.44
Dimensions (mm): 101.60 x 101.60
Thickness (mm): 3.00 ±0.25
Coating: BBAR (425-700nm)
Coating Specification: R _{avg} ≤0.5% @ 425 - 700nm
Edges: Seamed
Substrate: Float Glass
Surface Quality: 80-50
Transmission (%): 95.6 Average (typical)
Type: Protective Window
Wavelength Range (nm): 425 - 700
Length (mm): 101.60
Width (mm): 101.60

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant