

101.6 x 127mm, 45° AOI, Hot Mirror



Hot Mirrors

Stock #43-958 10 TO 12 DAYS



1



₹15,747.00

ADD TO CART

Qty 1-9
₹15,747.00
Qty 10+
₹13,920.00
Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°): 45.00
Coating: Hot Mirror, 45°
Substrate: ☐ BOROFLOAT®
Reflection (%):

>90, 750 - 1125nm
Dimensions (mm): 101.6 x 127.0
Surface Quality: 80-50
Thickness (mm): 3.30
Transmission (%): >85, 425 - 675nm
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.5
Coating Specification: Surface 1: 45° Hot Mirror Surface 2: None
Wavelength Range (nm): 425 - 1125
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
