

TECHSPEC[®] 101.6 x 326.7mm EFL 30° Protected Gold 100Å Off-Axis Parabolic Mirror



TECHSPEC Gold Off-Axis Parabolic Mirrors

Stock **#35-585** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹90,045.00

ADD TO CART

Qty 1-5

₹90,045.00

Qty 6+

₹81,041.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
101.60 +0.00/-0.38

Effective Focal Length EFL (mm):

326.69
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 609.60
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°): 30
Parent Focal Length PFL (mm): 304.8
Surface Figure, RMS: 1λ
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 700 - 10000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #83-977
Substrate: Aluminum 6061-T6
Y Offset (mm): 163.34
Reflected Wavefront, RMS: 2λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant