

TECHSPEC[®] 101.6mm Length, M6 Thread, Adjustable Post Holder



101.6mm Length, M6 Thread, Adjustable Post Holder, #84-354

Stock **#84-354** 6 In Stock

-

1

+

₹9,756

ADD TO CART

Volume Pricing	
Qty 1-9	₹9,756 each
Qty 10+	₹8,780 each
Need More?	Request Quote

Product Downloads

General

Metric

Type:

Physical & Mechanical Properties

30.00

Travel (mm):

101.60

Length (mm):

Threading & Mounting

M6 x 1.0		Mounting Threads:
Regulatory Compliance		
Compliant	RoHS 2015:	
Compliant	Reach 224:	
View	Certificate of Conformance:	
China	Country of Origin:	
Edmund Optics India Private Limited	Imported By:	

Product Details

- English and Metric Versions
- ¼-20 Base for English Version and M6 x 1 Base for Metric Version
- Provides Vertical Translation
- Compatible With 0.5" (12.7mm) Posts

TECHSPEC® Adjustable Height Post Holders are inexpensive alternatives to Z-axis and vertical stages. Featuring an adjustable ring that, when rotated, provides vertical translation, these post holders are ideal for applications that require vertical translation, but do not require the level of precision provided by a stage. These post holders are compatible with 0.5" (12.7mm) posts. TECHSPEC® Adjustable Height Post Holders have a ¼- 20 base for the English version and an M6 x 1 base for the Metric version. The post holders are available in three different lengths for both the English and the Metric versions.