

10.1mm FL, No IR-Cut Filter, f/2.8, Micro Video Lens



Stock #63-762 10 TO 12 DAYS



1



₹5,133.00

ADD TO CART

Qty 1-49

₹5,133.00

Qty 50+

₹4,089.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
13.40

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):
8.00

Horizontal Field of View @ Max Sensor Format: 36
Resolution, On-Axis: 81 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 54 lp/mm @ 20% Contrast
Resolution, Full Field: 64 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 10.10
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mbunt)
Aperture (f/#): f/2.8
Distortion (%): -0.57 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View