

10.60µm CWL, 25.0mm Diameter, 0.50µm FWHM, IR Bandpass Filter



Stock **#25-720** [CONTACT US](#)

[Additional Bandwidths](#)



1



₹51,939.00

ADD TO CART

Qty 1-9
₹51,939.00
Qty 10+
₹46,719.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 ±0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):

22.0
Center Wavelength CWL (nm): 10,600.00 ±40
Full Width-Half Max FWHM (nm): 500.00 ±50
Substrate: □ Germanium
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 80 (minimum)
Type: Bandpass Filter
Typical Applications: Carbon Dioxide Emission
Blocking Wavelength Range (nm): 200 - 14500
Center Wavelength CWL (μm): 10.60 ±0.04
Full Width-Half Max FWHM (μm): 0.50 ±0.05

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
