


1064nm, 18-23mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_1064_Q-20

See More by [AdlOptica](#)



Focal Flat Top Beam Shaper



Stock **#12-237** 10 TO 12 DAYS

⊖ 1 ⊕

₹264,480.00

ADD TO CART

Qty 1-4
₹264,480.00
Qty 5+
₹237,858.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
38

Design Wavelength DWL (nm): 1064
Diameter (mm): 64.00
Model Number: πShaper_1064_Q-20
Length (mm): 21.00
Transmission (%): >99
Type: Beam Shaper
Weight (g): 70
Wavelength Range (nm): 1020 - 1100
Input Beam Diameter, 1/e² (mm): 18 - 23
Maximum Input Power, CW (kW): 0.4
Inner Thread: M58 x 1
Outer Thread: M58 x 1
Compatible Adapter: #12-323
Input Beam Mode: TEM ₀₀
Typical Input Beam Mode Quality, M²: <1.5
Input Beam Divergence (mrad): ±20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant