

1064nm CWL, 25.4mm Dia., OD 7 Ultra Narrow Filter



Ultra Narrow Bandpass Filters



Stock **#36-642** [CONTACT US](#)

- 1 +

₹204,450.00

ADD TO CART

Qty 1-9
₹204,450.00
Qty 10+
₹185,745.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.30 ±0.1

Angle of Incidence (°):
0

Optical Density OD (Average): 7.00
Clear Aperture CA (mm): 21.30
Center Wavelength CWL (nm): 1,064.00
Full Width-Half Max FWHM (nm): 1.20
Substrate:  BOROFLOAT®
Minimum Transmission (%): >90
Coating: Hard Coated
Transmission (%): T _{abs} >90% @ 1064nm
Type: Bandpass Filter
Blocking Wavelength Range (nm): 300 - 1037, 1092 - 1100
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.0
Note: Filter Design: Multi-Cavity
Substrate Thickness (mm): 2.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant