

1064nm CWL, 1.00 FWHM, 25mm Dia. Ultra Narrow Filter



Stock #21-391

10 TO 12 DAYS

-

1

+

₹130,500.00

ADD TO CART

Qty 1-5
₹130,500.00
Qty 6+
₹117,015.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):

25.00 +0.00/-0.25

Angle of Incidence (°):

0

Clear Aperture CA (mm):

21.00

Center Wavelength CWL (nm):

1,064.00
Full Width-Half Max FWHM (nm): 1.00
Substrate: ☐ Soda Lime Glass & Filter Glass
Minimum Transmission (%): >50
Type: Bandpass Filter
Note: Filter Design: Two-Cavity
Substrate Thickness (mm): 6 +0.00/-0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant