

1064nm HP Flat Top Beam Shaper | πShaper 12_12_1064_HP_W

See More by [AdlOptica](#)



Stock **#21-101** [CONTACT US](#)

-

1

+

₹846,336.00

ADD TO CART

Qty 1-4
₹846,336.00

Qty 5+
₹761,685.00

Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm): 1064
Diameter (mm): 49.00
Entrance Beam Diameter, 1/e² (mm): 12.0 – 12.1
Model Number:

πShaper 12_12_1064_HP_W
Length (mm): 360.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <580
Wavelength Range (nm): 1020 - 1100
Style: Flat Top
Damage Threshold, By Design: ☐ 3 J/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 12.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant