

TECHSPEC® 10.8mm Motorizable Iris Spur Gear



10.8mm Motorizable Iris Spur Gear, #34-517

Stock #34-517 **20+ In Stock**

MRP ₹1,287

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹1,287 each
Qty 5-9	₹1,171 each
Qty 10-25	₹1,100 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Outer Diameter (mm):
10.8

Construction:
Brass

Pitch Diameter (mm):
10

Regulatory Compliance

Exempt RoHS 2015:

View Certificate of Conformance:

Contains SVHC(s) Reach 247:

Country of Origin:
Germany

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Fast Accurate Repeatable Motion
- Dual Control Gear and Lever Mechanics
- Removable Pin for OEM Integration
- Anti-Reflection (AR) Leaves Available
- Iris Diaphragm Mounts and Motor Sold Separately

TECHSPEC® High Performance Motorizable Irises are designed for integration into custom applications and for use in a lab environment. These irises include two methods for controlling the aperture size: one by a standard pin which enables standard angular deviation and the other that duplicates the movement of the pin by replicating the teeth of a spur gear on the inner housing of the iris. This feature allows for custom motion control in conjunction with a compatible spur gear. TECHSPEC® High Performance Motorizable Irises maintain fast, accurate, and repeatable movement to any location through the iris's range of motion. The 7mm, 12mm, 22mm, 28mm, and 34mm Max Aperture configurations are also available with Anti-Reflection (AR) Leaves.

Technical Information

