

TECHSPEC® 10mm 632.8nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#47-777** [CONTACT US](#)

-

1

+

₹20,967.00

ADD TO CART

Qty 1-5
₹20,967.00
Qty 6+
₹16,443.00
Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:

R _{abs} <0.25% @ 632.8nm
Construction: Cube
Design Wavelength DWL (nm): 632.8
Dimensions (mm): 10.0 x 10.0 x 10.0 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%): >95
S-Polarization Reflection (%): >99.5
Substrate:  N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View