

[See all 72 Products in Family](#)

TECHSPEC® 10mm Dia. Linear Polarizing Film (XP42-70)



Stock #71-359 **20+ In Stock**

1 MRP ₹1,564

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹1,564 each
Qty 11-25	₹1,231 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Polarization axis is parallel to notch on polarizer edge **Note:**

Physical & Mechanical Properties

10.00 +0.0/-0.3 **Diameter (mm):**

Thickness (mm):

0.72 ±0.1

Polarizing Film on PMMA **Construction:**

Optical Properties

Uncoated, protective film on both sides **Coating:**

9000:1 (nominal at 555nm) **Extinction Ratio:**

Polymer Film XP42-40 **Substrate:** □

Single: 42 ±2
Parallel: 36.4
Crossed: <0.004 (nominal at 555nm) **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

>99.98 (nominal at 555nm) **Polarization Efficiency (%):**

42 ±2 **Transmission, Single (%):**

36.4 **Transmission, Parallel (%):**

<0.004 (nominal at 555nm) **Transmission, Crossed (%):**

Environmental & Durability Factors

-10 to +60 **Operating Temperature (°C):**

Regulatory Compliance

View **Certificate of Conformance:**

Japan **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- **High-Temperature** Options Also Available


Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.


Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information



XP42 – Linear Polarizer



XP44 – Linear Polarizer

