

TECHSPEC® 10mm Dia x 15mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #47-754

10 TO 12 DAYS

-

1

+

₹10,353.00

ADD TO CART

Qty 1-5
₹10,353.00
Qty 6+
₹8,265.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00

Effective Focal Length EFL (mm):
15.00

Substrate:

N-BK7

f/#:

1.5
Numerical Aperture NA: 0.33
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 12.82
Center Thickness CT (mm): 3.30
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.70
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 7.75
Surface Quality: 60-40
Tilt Tolerance (mm): ±0.1 over H
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View