

TECHSPEC® 10mm H x 20mm L x 75mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #43-861

CLEARANCE

10 TO 12 DAYS

-

1

+

₹6,607.65

ADD TO CART

Qty 1+
₹6,607.65

Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):

75.00

Substrate: ☐

N-BK7

f/#:

7.5

Numerical Aperture NA:

0.07

Coating:

Uncoated

Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 73.72
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 10.0 x 20.0
Edge Thickness ET (mm): 1.67
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 38.72
Surface Quality: 60-40
Tilt Tolerance (mm): ±0.1 over H
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View