

TECHSPEC[®] 10mm N-SF11 Uncoated Equilateral Prism



Equilateral Prisms

Stock **#47-275** 20+ In Stock

-

1

+

₹9,720

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,720 each
Qty 6-25	₹8,775 each
Qty 26-49	₹7,785 each
Need More?	Request Quote

Product Downloads

General	
Equilateral Prism	Type:
Physical & Mechanical Properties	
10.00	Length of Face (mm):
10.00	Length (mm):

Dimensional Tolerance (mm):	
±0.1	
Optical Properties	
Coating:	
Uncoated	
Substrate: ☐	
N-SF11	
Surface Quality:	
40-20	
Angle Tolerance (arcmin):	
±2	
Image Orientation:	
Dispersion	
Wavelength Range (nm):	
400 - 2500	
Power (fringes) @ 632.8nm:	
2.50	
Irregularity (fringes) @ 632.8nm:	
0.50	

Regulatory Compliance	
Certificate of Conformance:	
View	
Country of Origin:	
Singapore	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- Ideal for Light Dispersion
- Sizes Ranging from 5 - 50mm
- Available Uncoated or Anti-Reflection Coated
- Additional [Equilateral Prism](#) Options Available

TECHSPEC® Equilateral Prisms feature three equal 60° angles and are often referred to as dispersing prisms. Equilateral prisms are ideal for wavelength separating applications and light dispersion. These prisms are available in sizes ranging from 5-50mm. Our TECHSPEC® Equilateral Prisms are offered uncoated or with a single layer MgF2 anti-reflection coating. Additional [Equilateral Prism](#) options are available.

Technical Information

