

TECHSPEC[®] 10mm TFL Mount Camera Lens Spacer



10mm TFL Mount Camera Lens Spacer



Stock #12-774 **14 In Stock**

-

1

+

₹2,880

ADD TO CART

Volume Pricing	
Qty 1+	₹2,880 each
Need More?	Request Quote

Product Downloads

General	
Lens Accessory	Type:
Physical & Mechanical Properties	
14.0	Total Length (mm):
45.0	Outer Diameter (mm):

10.0	Extension Length (mm):
Threading & Mounting	
TFL Mount	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- APS-C (27.9mm), TFL-Mount Lens or M40 Mount Lens
- Greater than 30 MegaPixels, 3.45µm Pixel Size Sensors
- High Resolution, Compact APS-C Lens (CA)
- 35mm to 100mm Focal Length

TECHSPEC® CA (Compact APS) Series Fixed Focal Length Lenses are designed for high-resolution large-format sensors. Covering the APS-C format sensors with a 28mm image circle, these lenses feature a [TFL Mount](#) or M40 Mount. TFL Mounts feature an M35 x 0.75 thread with a 17.5mm flange distance, and offer the same robustness and ease of use as a C-Mount. M40 Mounts feature a M52 x 0.75 thread with a 17.526mm flange and provide a robust, large-format mounting solution ideal for high-resolution and larger image sensors with improved mechanical stability and optical performance compared to smaller format mounts. TECHSPEC® CA Series Fixed Focal Length Lenses offer a compact size while accommodating large format sensors, making them ideal for machine vision and [factory automation](#) applications.

These lenses won the [3rd place 2020 Inspect Award](#) and the [Silver-Level 2020 VSD Innovators Award](#).