

TECHSPEC[®] 10mm Uncoated, Fused Silica High Tolerance RA Prism



TECHSPEC High Tolerance UV Fused Silica Right Angle Prisms

Stock **#47-201** 10 TO 12 DAYS



1



₹8,526.00

ADD TO CART

Qty 1-5

₹8,526.00

Qty 6+

₹7,673.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle Tolerance (arcsec):
±40

Coating:
Uncoated

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.0/-0.1
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 14.10
Length of Legs (mm): 10.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Wavelength Range (nm): 200 - 2200
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
