

TECHSPEC[®] 10mm VIS, Lateral Displacement Non-Polarized Beamsplitter



Lateral Displacement Beamsplitters

Stock #47-188 10 TO 12 DAYS

-

1

+

₹51,330.00

ADD TO CART

Qty 1-5
₹51,330.00
Qty 6+
₹41,064.00
Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (arcsec):
±5

Beam Separation (mm):
10.00

Clear Aperture (%):
80.00

Coating Specification:

R _{avg} <0.5% @ 430 - 670nm
Construction: Prism
Dimensional Tolerance (mm): ±0.1
Extinction Ratio: T _p - T _s <6%
P-Polarization Transmission (%): 45.00
Parallelism (arcmin): <2
Reflection/Transmission Tolerance (%): ±10
S-Polarization Reflection (%): 45.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Type of Optics: Non-Polarizing
Wavelength Range (nm): 430 - 670

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
