

TECHSPEC® 10mm VIS, Polarizing Cube Beamsplitter



TECHSPEC® Broadband Polarizing Cube Beamsplitters

Stock **#48-999** 10 TO 12 DAYS

⊖ 1 ⊕ **₹28,362.00**

ADD TO CART

Qty 1-5
₹28,362.00
Qty 6+
₹22,707.00
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
±3

Clear Aperture (%):
90

Coating Specification:
R_{avg} <0.5% @ 420 - 680nm

Construction: Cube
Dimensions (mm): 10.0 x 10.0 x 10.0 ±0.1
Extinction Ratio: 500:1
P-Polarization Transmission (%): >90
S-Polarization Reflection (%): >99
Substrate: ☐ N-SF11
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Linear Polarizer
Wavelength Range (nm): 420 - 680

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
